

Test Report

Report No.: A 905060-1



DANISH
TECHNOLOGICAL
INSTITUTE

Gregersensvej
DK-2630 Taastrup
Tel. +45 72 20 20 00
Fax +45 72 20 20 19

info@teknologisk.dk
www.teknologisk.dk

Assignor: Kvadrat A/S
Lundbergsvej 10
8400 Ebeltøft
Attn.: Lone Henriksen

Page 1 of 1
Chf/leln
Order no.: 905060
No. of appendices: 1

Subject: Curtain fabric designated: Apo, 100% Trevira CS / alubacking. (as per info from the assigner).

Sampling: The test material was sampled by the client and received at the Danish Technological Institute 05.12.2019

Method: See Appendix 1.

Period: The testing was completed 09.01.2020

Result: Individual results appear from Appendix 1.

Storage: The test material will be destroyed after 6 months, unless otherwise agreed.

Terms: The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

Date/place: 10.01.2020, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Signature: Test responsible

Co-signatory



Report no.: A 905060-1
 Appendix: 1
 Page: 1 of 2
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	101 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	131 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	161 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	191 Colour fastness: 4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	201 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	431 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	601 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	701 Colour fastness: 6

Report no.: A 905060-1
 Appendix: 1
 Page: 2 of 2
 Initials: Chf/IelN

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	761 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	931 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	961 Colour fastness: 4